


# **Dissolved Hydrogen Probe System**





## Accurate - Reliable - Small Dimensions - Easy Handling



The determination of the total dissolved hydrogen is one of the most important parameters for the analysis in **power plants**, waste water and in **industry**.

On the other hand, the total dissolved hydrogen concentration is an interesting parameter for scientists of several scientific departments. They use this parameter to understand chemical reactions and to optimise the process of the industrial production of chemicals.

But due to a lot of the hydrogen's inconvenient chemical properties, like high chemical reactivity, possible storage in metals and the fast concentration exchange between the liquid sample and the gaseous phase above (mostly air), the determination is difficult. Even though the sampling and the determination have been done very carefully, the results are uncertain and mostly disappointing.

All these disadvantages could be avoided, if the new Submersible Hydrogen Probe System is used for the accurate and reliable in-situ determination in depths of up to 100 m or in case of pressures of up to 10 bar.

The "heart" of this new probe is the hydrogen micro-sensor, which allows a very fast measurement with a very high local concentration resolution. For details please read the "general information for the hydrogen micro-sensor".

#### **Special Features:**

- Sensors for H<sub>2</sub> (amperometric micro-sensor), temperature and depth/pressure
- Very easy sensor exchange
- Windows based software for display of chemical/physical units and diagrams
- Free selection of displayed parameters (H<sub>2</sub>, T, pressure)
- Titanium made housing and protection cage
- Subconn titanium connector
- Very small dimensions (48 mm diameter, 440 mm total length)
- Low weight of 1 kg
- Small and low-weight cable (< 6 mm diameter)
- Low running costs for chemical sensor replacement

Sea & Sun Technology GmbH

Arndtstraße 9-13

D-24610 Trappenkamp, Germany Tel.: +49 (0) 4323/91 09 13

Fax: +49 (0) 4323/91 09 15 E-mail: email@sea-sun-tech.com

www.Sea-Sun-Tech.com

AMT Analysenmesstechnik GmbH

Joachim-Jungius-Strasse 9 D-18059 Rostock, Germany Tel.: +49 (0) 381/40 59 380 Fax: +49 (0) 381/40 59 383 E-mail: info@amt-gmbh.com

www.amt-gmbh.com

The **Submersible Hydrogen Probe system** is equipped with a precision microprocessor-controlled 4-channel 16 bit analogue to digital converter. The data are available as RS-232 signal (multi-conductor polyurethane covered cable) and optional as FSK signal modulated on constant current (single-conductor cable).

The probe can be powered by battery or DC power supply (9 to 30 V DC) when using the RS-232 output or by constant current with FSK telemetry output (coaxial connection) for longer distances. An interface for constant current supply is available.



Probe with removed protection cage. Sensors for H<sub>2</sub>, pH, temperature and depth.

## **Possible Sensor Equipment (on customers request)**

Sensors	Principle	Range	Accuracy	Resolution	Response time
Pressure	piezo-resistive full	10 bar	± 0,1 %	0,002 % FS.	150 ms
	bridge		FS		
Temperature	Pt 100	- 2 + 36 °C	± 0,05 °C	0,0006 °C	1 s
pН	single rod elec-	0 14 pH	$\pm$ 0,02 pH	0,0002 pH	1 s
	trode				
$H_2$	Amperometric	0,2 μg/l0,5 mg/l	2% of	$0.1 \mu g/1 H_2$	< 1s
	micro-sensor	2 μg/l1 mg/l	reading	0,4 μg/l H <sub>2</sub>	

### Technical data of the probe system

Feature	Online Probe	Memory Probe				
Dimensions:	Ø 48, length: 400 mm	Ø 48, length: 440 mm				
Weight on air:	1,1 kg	1,3 kg				
Material:	Titanium	Titanium				
Connector:	Subconn MCBH4M	Subconn MCBH5M				
Power Supply:	External 930 Volt DC	External: 716 V DC				
		Internal Battery: 15 V DC				
Current consumption:	12 mA at 12 V DC	External power supply: 15 mA Li-battery (3,6 V): approx. 2035 mA Alkbattery (1,5 V): approx. 5090 mA				
Data output	Serial port RS232, option: FSK-telemetry	Serial port RS232				
Memory capacity:	none	8 MB (approx. 350.000 data sets)				
In view of our policy of continual improvement, the design and specifications of our products may vary from those illustrated in this brochure.						

Your distributor: AMT Analysenmesstechnik GmbH

Joachim-Jungius-Strasse 9, D-18059 Rostock, Germany Tel.: +49 (0) 381/40 59 380, Fax: +49 (0) 381/40 59 383 E-mail: amt-gmbh@t-online.de www.amt-gmbh.com